



GammaGuard® CE  
Features Video



GammaGuard® CE  
Brand Page

## GammaGuard® CE

Sterile garments designed with comfortable fabric and a superior liquid and particulate barrier.

All GammaGuard CE® garments are individually packaged and sterilized to a  $10^{-6}$  sterility assurance level (SAL). This helps prevent workplace contamination and cross contamination of products or materials. Low-linting fabric helps reduce the release of unwanted particulates, while tunnelized elastic also contains particle shed.


### Available Garments



**Coverall with Tunnelized Elastic Wrists & Ankles**

#CE11013CIS

Sizes: Small - 4XL  
25 per case



**Coverall with Attached Hood & Boots**

#CE11019CIS

Sizes: Small - 4XL  
25 per case



**Frock, No Pockets, Tunnelized Wrists**

#CE11026CIS

Small - 4XL  
50 per case



**Full Face Hood with Tunnelized Elastic Face**

#CE11063CIS

Size: Universal  
100 per case



**Sleeves, 21.5" Length Tunnelized Elastic on Both Ends**

#CE11065CIS

Size: Universal  
100 pairs per case



**Non-Skid Shoe Covers**

#CE11101CIS

Size: Large  
Non-Skid Soles  
200 pairs per case

#CE11102CIS

Size: XL  
Non-Skid Soles



**Non-Skid Boot Covers**

#CE11104CIS

Size: Large  
Non-Skid Soles  
100 pairs per case

#CE11106CIS

Size: XL  
Non-Skid Soles



(800) 345-5972



2400 Skyline Dr., Suite 400  
Mesquite, Texas 75149



int-enviroguard.com

### Benefits

In a cleanroom environment, maintaining sterility is critical for keeping products, processes, and materials contamination-free. GammaGuard® CE cleanroom apparel is designed with varying levels of protection to help keep you safe based on your cleanroom standards.


All garments and cleanroom suits are clean processed using the Sterile-Don™ packaging process, meaning all loose particles have been removed from the clothing before packaging.

### Physical Testing

TEST	METHOD	RESULT
Weight, oz/y <sup>2</sup>	ASTM D3776	1.8
Ball Burst Strength (lbs)	ASTM D3787	21
Tensile Strength (lbs) Machine Direction	ASTM D5034	15
Tensile Strength (lbs) Cross Direction	ASTM D5034	24.5
Tensile Strength (lbs) Trapezoidal - Machine Direction	ASTM D1117	2.4
Tensile Strength (lbs) Trapezoidal - Cross Direction	ASTM D1117	5.6
Air Permeability (cfm)	ASTM D737	<0.55
Helmke Drum Particle Test	IEST-RP-CC003	Category 1




**Bound Seams**





**Tunnelized Elastic**





**Sterility Assurance**


- 

**Raise your Standards**  
GammaGuard® CE is made in an ISO-13485 certified facility. All garments are sterilized to a 10<sup>-6</sup> SAL, which is the highest level possible.
- 

**Tear-resistant Fabric**  
Our proprietary fabric is tear-resistant and keeps users cooler than competitive fabrics.
- 

**Trust the Process**  
Sterile-Don™ packaging protects against contamination during donning.
- 

**Quality Assurance**  
A certificate of sterility is included in each case.
- 

**Decrease Particle Shed**  
Tunnelized elastic is encapsulated to capture particle shed & eliminate raw edges that can generate and shed particulates.
- 

**Bound Seams are Strong Seams**  
A reinforced outer binding is tightly sewn over each seam to strengthen it & eliminate raw edges that can generate particulates.